



## Technical data

1R20X25X125

Inner rings

Needle roller bearing, inner ring

| PRODUCT DEFINITION             |          |
|--------------------------------|----------|
| Brand                          | NTN      |
| d - Internal diameter          | 20 mm    |
| B - Bearing/Inner ring width   | 12,5 mm  |
| F - Under roller diameter      | 25 mm    |
| rs - Min fillet radius         | 0,3 mm   |
| Lubrication hole on inner ring | Non/No   |
| t - IR chamfer length          | 1,8 mm   |
| Precision class                | P0       |
| Mass                           | 0,016 kg |

| ABUTMENT                                    |        |
|---------------------------------------------|--------|
| da min - Min shoulder diameter IR           | 22 mm  |
| ras max - Max shaft & housing fillet radius | 0,3 mm |