

087U - MALE PROBE BSP PARALLEL



TECHNICAL SPECIFICATIONS

maximum working pressure	16 bar 2 MPa 232 psi
working temperature	-20 to 60 °C -4 to 140 °F 253 to 333 °K
nozzle	STEEL NICKEL PLATED
sealing washer	TECHNICAL POLYMER

Part Nb	(MM)	Flow Rate (l/mn)	C	Pack Qty
	All ▾	All ▾	All ▾	All ▾
9087U06 13	5.5	1,250	G1/4	5
9087U06 17	5.5	1,250	G3/8	5
9087U06 21	5.5	1,250	G1/2	5
9087U08 13	8	2,400	G1/4	5
9087U08 17	8	2,400	G3/8	5
9087U08 21	8	2,400	G1/2	5

Part Nb	C	E (mm)	F (mm)	L (mm)	L1 (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
9087U06 13	G1/4	7	16	37	24	.025
9087U06 17	G3/8	7	20	37	24	.032
9087U06 21	G1/2	9	24	39	24	.048
9087U08 13	G1/4	7	16	38	26	.03
9087U08 17	G3/8	7	20	39	26	.036
9087U08 21	G1/2	9	24	42	26	.058