



ENGLISH

Datasheet

Stock No: 403-370

## RS Pro D-sub Interface Module



### Product Details

#### D Subminiature

Screw terminal interface modules with connectors suitable for interfacing electrical cabling to I/O cards and electronic equipment. Designed to mount on standard BS 5584:1978 'DIN' rail. Orange polyamide 6.6 housings with gold plated connector contacts

Temperature range -20 to +50°C

Height 62mm, Width 70mm

Length: 9-way (45mm), 15-way (65mm), 25-way (90mm), 37-way (110mm)

Suitable CSA: (Flexible)2.5mm<sup>2</sup>, (Solid)4 mm<sup>2</sup>

**Interface Modules (DIN Rail Mounting)**



ENGLISH

## Specifications:

Gender	Female
Number of Contacts	9
Connector Type	D-sub
Mounting Type	DIN Rail Mount
Voltage Rating	50 V
Current Rating	1A
Cable CSA	4mm <sup>2</sup>
Dimensions	45 x 70 x 62mm
Depth	62mm
Length	45mm
Minimum Operating Temperature	-20°C
Width	70mm
Maximum Operating Temperature	+50°C