

BIZ1 - Bizweld Work FR Coverall

Collection: Bizweld™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizweld Work: 100% Cotton, 330g

Outer Carton: 12

Product information

Voted the number one favourite coverall in the welding industry, our best selling Bizweld coverall is ideal for offering complete protection to workers exposed to heat. The generous fit provides comfort and allows the wearer to work unhindered whilst ample storage space, rule pocket and concealed mobile phone pocket hold equipment securely and safely.

Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

IEC 61482-2 IEC 61482-1-1 (ELIM 8.3 CAL/CM², ATPV 10.9 CAL/CM²)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM² (HAF = 80.4%))



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Concealed stud front for easy access
- Chest pockets with stud closure
- Stud adjustable cuffs for a secure fit
- Rule pocket
- Radio loop for easy clipping of a radio
- Concealed phone pocket
- 6 pockets for ample storage
- CE-CAT III
- CE certified

BIZ1 - Bizweld Work FR Coverall
Commodity Code: 6211321000

Test House
SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/12872-03/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
BIZ1NATS	Navy Tall	43.0	28.0	52.0	1.2000	0.0626	5036108039319	25036108607338
BIZ1NATM	Navy Tall	43.0	28.0	52.0	1.3400	0.0626	5036108039326	25036108607321
BIZ1NATL	Navy Tall	43.0	28.0	58.0	1.3200	0.0698	5036108039333	25036108607314
BIZ1NATXL	Navy Tall	43.0	28.0	58.0	1.3800	0.0698	5036108039340	25036108607345
BIZ1NATXXL	Navy Tall	43.0	28.0	58.0	1.5100	0.0698	5036108039357	25036108607352
BIZ1NATXXXL	Navy Tall	43.0	28.0	58.0	1.4900	0.0698	5036108039364	25036108607369
BIZ1NAT4XL	Navy Tall	43.0	28.0	58.0	1.6300	0.0698	5036108039371	25036108607307
BIZ1NAT5XL	Navy Tall	43.0	28.0	58.0	1.6200	0.0698	5036108142002	25036108688887