Parker Product Datasheet



Quick coupling system with nominal diameter 7.2 for pneumatic applications up to 35 bar. Available in brass sleeve or polymer.

PART NUMBER: 26KETF06MPN
COUPLING HALF: Coupler
FUNCTION: Self-Venting
CONNECTION TYPE: Hose Barb
BODY MATERIAL: Brass
CONNECTION SIZE: 6 MM

PRODUCT OVERVIEW

Parker's Basic Quick Coupling Series 26 is an industrial brass coupling with European profile. Coupling system with single-hand operation and standard-valve. Small mass size. The ergonomic sleeve (available in Brass or Polymer) design prevents dirt on the valve body.

Markets:
- General Industrial
- Industrial manufacturing equipment

Features/Benefits:
- Industrial coupling with European profile, most representative profile worldwide
- Single-hand operation for easy and fast connection

TECH SPECIFICATIONS

QUANTITY PER BOX	5
COUPLING HALF	Coupler
OPERATION TYPE	Sleeve
PRODUCT STYLE	Quick-Connect
OUTSIDE DIAMETER	31 mm
REGION OF ORIGIN	Germany
SEAL MATERIAL	NBR
BODY MATERIAL	Brass
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air)
BRAND	Parker
MAXIMUM OPERATING TEMPERATURE	60 °C
APPLICATION	Mobile & Defence
PLATING TYPE	Nickel-Plated
PRODUCT SERIES	Series 26
CONNECTION SIZE	6 mm
MINIMUM OPERATING TEMPERATURE	-20 °C
VALVE TYPE	Standard Valve
WEIGHT	0.098 kg
INTERCHANGE TYPE	European Profile
MAXIMUM OPERATING TEMPERATURE	140 °F
APPLICATION	Trucks & Trailers
DIVISION	Low Pressure Connectors Europe Division
DIAMETER	7.4 mm (nominal)
BRAND	Rectus

MINIMUM OPERATING TEMPERATURE	-4 °F
APPLICATION	Energy Management
SLEEVE MATERIAL	Brass
INDUSTRY	Electronics
MAXIMUM OPERATING PRESSURE	174 psi
APPLICATION	Air & Gas Compressor
TECHNOLOGY	Pneumatics
FLOW RATE	830 L/min (air)
MAXIMUM OPERATING PRESSURE	12 bar
PRODUCT TYPE	Pneumatic Quick Couplings
INDUSTRY	General Industrial
LENGTH	71 mm
HEX SIZE	22 mm
FUNCTION	Self-Venting
VALVE INCLUDED	Yes
INDUSTRY	Transportation
COMPATIBLE FITTING	Series 25 Plug
APPLICATION	Electronics
CONNECTION TYPE	Hose Barb
DIVISION	Low Pressure Connectors Europe Division