



Oil

Low Chemical Protection



Light Duty

Ultralight abrasion-resistant gloves with special oil-repellent capabilities

- **Enhanced grip:** Three quarter-dipped coating featuring Improved ANSELL GRIP™ Technology provide 20% higher grip* in wet and oily conditions minimizing required force for safer handling
- **Specialized protection:** Improved HyFlex® 11-925 industrial gloves' RIPEL™ Liquid Repellence surface barrier averts skin contact with oil or chemicals for increased oil protection and permeability
- **Increased flexibility:** HyFlex® 11-925 safety gloves' ergonomic hand shape and ultralight fine-gauge liner help reduce hand fatigue and augment dexterity
- **Elevated comfort:** The blend of Spandex® and Nylon® in these HyFlex® gloves' liner also grants them a “second skin” sensation of lightness and comfort
- **Touchscreen compatible:** These industrial gloves work with multiple touchscreen devices – no need to remove them when switching between tasks for workplace safety
- **Enhanced defenses:** HyFlex® 11-925 industrial gloves feature EN407 heat contact level 1 resistance allowing occasional handling of hot objects at temperatures up to 100°C/212°F (for 15 seconds)



Industries

- Automotive
- Machinery and Equipment
- Chemical
- Agriculture
- Oil and gas

Applications

- Assembly & inspection of components
- Assembly and disassembly of equipment
- Assembling and mounting components
- Inspection (picking, checking and marking)
- Mounting and dismantling
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Loading trucks & vehicles
- Product shipping, transport and delivery

Key Features

- **Improved ANSELL GRIP™ coating:** up to 20% higher grip in wet and oily conditions*
- **Three-quarter dipping:** For defensive coating with ample grip
- **Ultralight fine-gauge liner:** Highly flexible, dexterous hand protection

*vs previous technology version

Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-925	Finishing: ¾ Coated Coating Material: Nitrile Liner Material: Nylon, Spandex Cuff Style: Knitwrist	18	6, 7, 8, 9, 10	205-250 mm/ 8.07-9.84 inches	Black	12 pairs/bag, 12 bags/carton

Technologies



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.