1520228-4 ! PENDING OBSOLESCENCE

Alcoswitch

TE Internal #: 1520228-4

TE Internal Description: 7360K8=BULKPACK 10 TOGGLE SW

View on TE.com >

Switches > Toggle Switches







Contact Current Rating: **10 A**

Configuration (Pole-Throw): **Double Pole - Single Throw**

Operating Function: **On Off**

Number of Positions: **2**

Operating Voltage: **250 VAC**

Features

Product Type Features

Switch Connection Type	Screw Terminal
Toggle Style	Baton
Switch Type	Power Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Double Pole - Single Throw
Operating Function	On Off
Number of Positions	2

Electrical Characteristics

Contact Current Rating	10 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Vertical
Bushing Style	Threaded
Bushing Thread Size	15/32-32

Mechanical Attachment

Product Mount Type	Panel Mount

Dimensions

Toggle Length	17.04 mm[.671 in]
Bushing Length	11.5 mm[.453 in]

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (2.59% in component) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1520117-2
8910K97=10 AMP TOGGLE



TE Part # 1520228-2
7359K3




TE Part # 2-1520228-4
7360K8=T-PAK for 0-1520228-4



TE Part # 1520228-3
7360K7=10 AMP TOGGLE SWITCH/DI



TE Part # 1825476-1
7360K8 MODIFIED SHELF ITEM ONL



TE Part # 1520120-1
8910K194=20 AMP TOGGLE



TE Part # 1520228-7
8909K23=7360K8 MOD




TE Part # 2-1520228-5
7361K5=T-PAK for 0-1520228-5



TE Part # 1520228-8
8910K12=7360K8 W/ SPADE TERMIN




TE Part # 2-1520228-3
7360K7=T-PAK for 0-1520228-3



TE Part # 1520117-1
8910K94=10 AMP TOGGLE



TE Part # 1520228-5
7361K5=10 AMP TOGGLE SWITCH/DI




TE Part # 1520238-1
8630K50=8 AMP ROCKER

Customers Also Bought



TE Part #1393143-6
27E122=SOCKET,KRP,8,SCW,SURF-MOUNT



TE Part #54123-1
CPC,13 LONG TUBE



TE Part #206039-1
CPC PLUG ASSEMBLY SIZE 17-28



TE Part #350550-3
UMNL SOK 20-14 PTPPHBZ L/P



TE Part #1-480305-0
03P CMNL CAP HSG F/H NATL




TE Part #208721-1
RECEPT ASSY,SZ 14,CMC



TE Part #34160
TERMINAL,PG R 16-14 8



TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals



TE Part #58423-1
DIE, RBY IS9252

Documents

Product Drawings

7360K8=BULKPACK 10 TOGGLE SW

English

CAD Files

Customer View Model

ENG_CVM_CVM_1520228-4_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1520228-4_B1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1520228-4_B1.2d_dxf.zip

English

3D PDF

3D

3D PDF

English

Customer View Model

ENG_CVM_1520228-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_1520228-4_B.3d_stp.zip

English

Customer View Model

ENG_CVM_1520228-4_B.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

Agency Approvals

UL

English

UL

English

UL

English