

Features

- **Loading Bays:** Absorbs impact to prevent damage to goods, vehicles, and docking infrastructure
- **Warehouses:** Shields walls and machinery from forklift and equipment collisions.
- **Factory Production Lines:** Protects sensitive equipment and workspaces from wear and tear.

RS PRO Standard Rubber D-Fender 3m Length x 92mm Width x 95mm Height SBR/NR

Vendor Partcode.: 0688178



RS PRO is our own brand range and brings you a wide range of high-quality, great value products offering you more choice. Trusted by engineers all over the world, every part of every RS PRO product has been rigorously tested against demanding industry standards; they're only given the RS PRO Seal of Approval if we're confident of their exceptional quality, which means you can be confident too.

RS PRO NR/SBR D-Fenders are expertly crafted from high-quality NR and SBR rubber, offering superior durability and impact resistance in industrial settings. Engineered specifically for loading bays, warehouses, and factory environments, these heavy-duty fenders safeguard infrastructure from accidental impacts, minimizing damage to walls, equipment, and vehicles. Their versatile installation allows them to be mounted on floors or walls, ensuring effective protection across large surface areas.

Unlike many other options, RS PRO D-fenders come without pre-drilled holes, allowing for customized placement to suit unique applications. For a more convenient setup, we offer an optional pre-drilled service upon request—simply contact our team for details.

Specifications

Material	SBR/NR
Colour	Black
Length	3000mm
Width	92mm
Height	95mm
Wall Thickness	20mm
Hardness	80ShA
Density (g/cm³)	1.9
Weight (Kg)	33

Approvals

Standards Met	REACH
----------------------	-------