



professionalLINE Cable Reel with Powerblock IP44 33+5m H07RN-F 3G1,5

Basic data:

Product number:	9211380100
EAN:	4007123637546
Article type:	KC 3100



- With mobile power block and four additional sockets for convenient use on scaffolds, roofs, etc.
- Power block with visual readiness indicator, hinged metal suspension hook and strap.
- In addition to the power block: four Schuko sockets, splash water protected, with self-closing covers.
- Pro-reel with rollover protection on all sides.
- Stable on all four sides, perfect cable management from all four sides.
- Large, sturdy fold-down turning handle rolls cables in and out effortlessly.
- Sturdy carrying handles and plug storage compartments on all four sides.
- The body and reel are made of Rubbabren, an extremely shock- and impact-resistant plastic and rubber mix. For permanent use in toughest conditions.
- Cold-resistant to -25 °C.
- RN cable is very robust, oil resistant and especially suited for professional use and on site.
- With extra robust earthed plug.
- With thermal cut-out protection against overheating or overload.
- Cable reel with 5 m cable for connecting to the power source.
- With visual readiness indicator in the socket insert.
-

Productline's value propositions:

Cable: H07RN-F 3G1,5

Cable colour: black

Colour: black, grey, orange,

Cable diameter: 1.5 mm²

Cable length: 33m / + 5m

Max. current carrying capacity – e: 16 A

Cable quality: Rubber-Neoprene

Degree of protection (IP): IP44

Number of sockets: 4

Datasheet – 9211380100