

Previously known as: MERCURY™43-113



Heat



Welding



Medium Duty

Heat- and cut-resistant gloves, granting wearers complete hand and wrist protection

- **Advanced protection:** ActivArm® 43-113 safety gloves feature Dupont™ Kevlar® outer yarn and can intermittently handle dry hot objects up to 350°C/660°F, resisting radiant, convective and contact heat
- **Specialized defenses:** ActivArm® 43-113 flame-resistant gloves do not melt, drip or propagate flames as they self-extinguish, protecting hands, wrists and arms from serious skin injuries
- **Advanced cut resistance:** They also satisfy ANSI A5/EN ISO E cut resistance standards, making them an ideal choice for handling machinery and equipment
- **Heightened comfort:** ActivArm® 43-113 protective gloves are cotton-lined, boosting their absorbency and dexterity
- **Enhanced features:** Their long knitwrist cuff also ensures greater forearm and wrist protection



Industries

- Machinery and Equipment

Applications

- Handling hot glass, bottles and panes
- Handling hot metal castings
- Rubber processing, vulcanizing and calendering
- Demoulding rubber tyres, belts and profiles
- Removing products from autoclaves

Previously known as: MERCURY™43-113

Key Features

- Dupont™ Kevlar® outer yarn: Tolerates dry handling up to 350°C/660°F
- Self-extinguishing design: For reliably flame-resistant work gloves
- ANSI/ISEA 105-2024 CUT A5 and EN ISO E certification: Offers superb hand protection.

Technologies

Kevlar®

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



0493



EN388: 2016



154XE

EN 407



43421X

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm® 43-113	Liner Material: Kevlar para aramid with silica fiber core Cuff Style: Knitwrist	7	6, 7, 8, 9, 10, 11	330-381 mm/12.99-15 inches	6 pairs/bag, 6 bags/carton Sizes available in NA/LAC: 6-10 Sizes available in EMEA/APAC: 9-11

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.