

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151360503](#)
Status: **Active**
Overview: MicroClasp™ Wire-to-Board System
Description: MicroClasp™-to-MicroClasp™ Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 5 Circuits, White

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	15136
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MicroClasp™-to-MicroClasp™
Overview	MicroClasp™ Wire-to-Board System
Product Literature Order No	987651-6143
Product Name	MicroClasp™ OTS
UPC	191128149556

Physical

Cable Length	300.00mm
Circuits (Loaded)	5
Color - Resin	White
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	7.567/g
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.28mm
Wire Size AWG	22
Wire/Cable Type	UL 1061

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	2012341708-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[15136](#) Series

Mates With

[55932](#) Vertical Header, [55935](#) Right Angle
Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION