

## FEATURES

- Momentary general-purpose foot switch with thermoplastic casing
- Contact voltage rating of 24 V
- Silver contact material with double pole single throw (DPST) configuration
- Contact current rating of 3 A
- IP rating of IPX7
- Black and grey colour
- Supplied with 2 m of black 3-core cable
- Dimensions of 150mm x 207mm x 42mm
- 2 x Normally open contacts - Linked commons
- RoHS (Restriction of Hazardous Substances) compliant

## RS PRO General Purpose Momentary Foot Switch - Thermoplastic Case Material, Double Pole Single Throw (DPST), 3 A

RS Stock No.: 808-6992



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO general-purpose momentary footswitch with double pedals and a double pole, single throw (DPST) switch is suitable for conditions where it's a safer option for operating machinery than a hand switch. As it's waterproof, it's also well suited to areas that might be wet. The dual pedals are used to change contacts within an electrical circuit.

This product features a durable and strong glass-filled plastic body. A low-profile, rear-hinged switch means you'll find it comfortable to use, and it also features an all-plastic construction, raised tread pattern and anti-slip pad.

## General Specifications

<b>Contact Configuration</b>	Double Pole Single Throw (DPST)
<b>Switch Operation</b>	Momentary
<b>Case Material</b>	Thermoplastic
<b>Switch Environment</b>	General Purpose
<b>Contact Material</b>	Silver
<b>Colour</b>	Black, Grey
<b>Cable Connection</b>	2 meters of 3 core black cable free wire ends
<b>Applications</b>	Foot switches are commonly used in applications where hands-free control is more practical or safer.

## Electrical Specifications

<b>Contact Voltage Rating (AC)</b>	24V
<b>Contact Voltage Rating (DC)</b>	24V
<b>Contact Current Rating</b>	3A

## Mechanical Specifications

<b>Dimensions</b>	150mm x 207mm x 42mm
<b>Length</b>	150mm
<b>Height</b>	42mm
<b>Width</b>	207mm
<b>Weight</b>	0.505kg Approx.

## Operation Environment Specifications

<b>Operating Temperature</b>	-20°C to +60°C
------------------------------	----------------

## Protection Category

<b>IP Rating</b>	EN 60529 IPX7
------------------	---------------

## Approvals

<b>Standards Met</b>	Footswitch : EN 60950, EN 60601-1:2016, UL 60601-1:2005, ANSI/AAMI ES60601-1:2005/(R)2012CSA-C22.2 No. 60601-1:14, UL File No. E353500
----------------------	--



## Images & Reference Dimensions

