

Han CGM-M M16x1,5 D. 4-8mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5028
Specification	Han CGM-M M16x1,5 D. 4-8mm
HARTING eCatalogue	https://harting.com/19000005028

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-M
Type of accessory	Cable gland

Technical characteristics

Wrench size	17 19
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M16
Clamping range	4 ... 8 mm
Width across corners	20.8 mm

Material properties

Material (cable glands)	Brass
Material (seal)	NBR
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	19.767 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140193031
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431