

**GLASS GG GUARD**

*Coated Outside*



**Industry Compliant Coated  
Shatterproof Lamps**

**In partnership with BRC Global Food Standards**

All products where applicable are subject to the WEEE recycling charge  
Our high quality GlassGuard® coating is applied to lamps from the leading brands: Philips, GE, Osram & Sylvania

## GlassGuard BlackBand® Coated T5 Std Fluorescent Lamps

Length	Stock Code	Description
300mm	835/S	12" 8w White 35
	833/S	12" 8w Cool White 33
	883/S	12" 8w Col 830
	884/S	12" 8w Col 840
525mm	1335/S	21" 13w White 35
	1333/S	21" 13w Cool White 33
	1384/S	21" 13w Col 840
563mm	1483/S	14w Col 830
	1484/S	14w Col 840
	14865/S	14w Col 865
	2483/S	24w Col 830
	2484/S	24w Col 840
	24865/S	24w Col 865
863mm	2183/S	21w Col 830
	2184/S	21w Col 840
	21865/S	21w Col 865
	3983/S	39w Col 830
	3984/S	39w Col 840
	39865/S	39w Col 865
1163mm	2883/S	28w Col 830
	2884/S	28w Col 840
	28865/S	28w Col 865
	5483/S	54w Col 830
	5484/S	54w Col 840
	5484EXTRA/S	54w Col 840 Extra Life
	54865/S	54w Col 865
1463mm	3583/S	35w Col 830
	3584/S	35w Col 840
	35865/S	35w Col 865
	4983/S	49w Col 830
	4984/S	49w Col 840
	4984EXTRA/S	49w Col 840 Extra Life
	49865/S	49w Col 865
	8083/S	80w Col 83
	8084/S	80w Col 840
	8084EXTRA/S	80w Col 840 Extra Life
	80865/S	80w Col 865

## GlassGuard BlackBand® Coated T8 Std Fluorescent Lamps

Length	Stock Code	Description
18" 450mm	1535/S	15w White 35
	1583/S	15w Col 830
	1584/S	15w Col 840
2ft 600mm	1835/S	18w White 35
	18835/S	18w Col 835
	1883/S	18w Col 830
	1884/S	18w Col 840
	1884EXTRA/S	18w Col 840 Extra Life
	1884EXT/S	18w Col 840 Extreme Life
	18865/S	18w Col 865
	18965/S	18w Col 965 Daylight
1879/S	18w Col 79 Gourmet	
3ft 900mm	3035/S	30w White 35
	30835/S	30w Col 835
	3083/S	30w Col 830
	3084/S	30w Col 840
	3079/S	30w Col 79 Gourmet
4ft 1200mm	3635/S	36w White 35
	36835/S	36w Col 835
	3683/S	36w Col 830
	3684/S	36w Col 840
	3684EXTRA/S	36w Col 840 Extra Life
	3684EXT/S	36w Col 840 Extreme Life
	3684R/S	36w Col 840 Reflex
	36865/S	36w Col 865
	36965/S	36w Col 965 Daylight
3679/S	36w Col 79 Gourmet	
5ft 1500mm	5835/S	58w White 35
	58835/S	58w Col 835
	5883/S	58w Col 830
	5884/S	58w Col 840
	5884EXTRA/S	58w Col 840 Extra Life
	5884EXT/S	58w Col 840 Extreme Life
	5884R/S	58w Col 840 Reflex
	58865/S	58w Col 865
	58965/S	58w Col 965 Daylight
5879/S	58w Col 79 Gourmet	
6ft 1800mm	7035/S	70w White 35
	70835/S	70w Col 835
	7083/S	70w Col 830
	7084/S	70w Col 840
	7084EXTRA/S	70w Col 840 Extra Life
	7084EXT/S	70w Col 840 Extreme Life
	70865/S	70w Col 865
	70965/S	70w Col 965 Daylight

## GlassGuard BlackBand® Coated T8 Watt-Miser

Length	Stock Code	Description
2ft 600mm	1683/S	16w Col 830 Watt-Miser
	1684/S	16w Col 840 Watt-Miser
4ft 1200mm	3283/S	32w Col 830 Watt-Miser
	3284/S	32w Col 840 Watt-Miser
5ft 1500mm	5183/S	51w Col 830 Watt-Miser
	5184/S	51w Col 840 Watt-Miser
6ft 1800mm	6383/S	63w Col 830 Watt-Miser
	6384/S	63w Col 840 Watt-Miser

## GlassGuard BlackBand® Coated Insect & Germicidal Lamps

12" 300mm	128WBL350/S	12" 8w BL350
18" 450mm	1815WBL350/S	18" 15w BL350
2ft 600mm	2420WBL350/S	2ft 20w BL350
2ft 600mm	2440WBL350/S	2ft 40w BL350
	FC22WBL350/S	FC 22w Circline BL350
	25WUBEND	4 PIN 25w U Bend BL350
	40WUBEND	4 PIN 40w U Bend BL350
	PL11WLYNX-S	2 PIN 11w LYNX BL350
12" 300mm	8TUV/S	12" 8w Germicidal UVC
18" 450mm	15TUV/S	18" 15w Germicidal UVC
3ft 900mm	30TUV/S	3ft 30w Germicidal UVC
4ft 1200mm	36TUV/S	4ft 36w Germicidal UVC

## GlassGuard BlackBand® Coated BlackLight Blue Lamps

2ft 600mm	1808/S	18w BLB
4ft 1200mm	3608/S	36w BLB

## UV Blocking T8 Fluorescent Lamps

2ft 600mm	18WG10	18w Gold/Yellow
2ft 600mm	18WC10	18w Clear U.V Block
3ft 900mm	30WG10	30w Gold/Yellow
3ft 900mm	30WC10	30w Clear U.V Block
4ft 1200mm	36WG10	36w Gold/Yellow
4ft 1200mm	36WC10	36w Clear U.V Block
5ft 1500mm	58WG10	58w Gold/Yellow
5ft 1500mm	58WC10	58w Clear U.V Block
6ft 1800mm	70WG10	70w Gold/Yellow
6ft 1800mm	70WC10	70w Clear U.V Block

## GlassGuard® Coated Halogen Flood Lights

Length	Stock Code	Description
Std	FLOOD375W/S	375w Energy Saver Flood Light
Std	FLOOD300W/S	300w Flood Light

## GlassGuard® Coated HID Mercury Lamps

Std	80HPLN/S	80w MBF/U
Std	125HPLN/S	125w MBF/U
Std	250HPLN/S	250w MBF/U
Std	400HPLN/S	400w MBF/U

## GlassGuard® Coated HID Metal Halide Lamps

Std	HPI250W/S	250w Philips Metal Halide
Std	HPI400W/S	400w Philips Metal Halide
Std	250WHIE00326/S	250w Venture Metal Halide
Std	400WHIE00327/S	400w Venture Metal Halide

## GlassGuard® Coated Incandescent Lamps

Std	25W BCP/S	25w BC Pearl
Std	40WBCP/S	40w BC Pearl
Std	60WBCP/S	60w BC Pearl
Std	25WESP/S	25w ES Pearl
Std	40WESP/S	40w ES Pearl
Std	60WESP/S	60w ES Pearl
Std	60WBCR64/S	60w BC R64 Reflector Spot
Std	60WBCR80/S	60w BC R80 Reflector Spot
Std	60WESR64/S	60w ES R64 Reflector Spot
Std	60WESR80/S	60w ES R80 Reflector Spot
Std	40WESCGOLF/S	40w ES Clear 45mm Round
Std	60WESCGOLF/S	60w ES Clear 45mm Round
Std	60WESCAN/S	60w ES Clear Candle
Std	60WBCCAN/S	60w BC Clear Candle

## GlassGuard® Coated Compact Fluorescent Lamps

Length	Stock Code	Description
Std	10WPLC2P83	10w PL-C 2 Pin Col 83
Std	10WPLC2P84	10w PL-C 2 Pin Col 84
Std	13WPLC2P83	13w PL-C 2 Pin Col 83
Std	13WPLC2P84	13w PL-C 2 Pin Col 84
Std	18WPLC2P83	18w PL-C 2 Pin Col 83
Std	18WPLC2P84	18w PL-C 2 Pin Col 84
Std	26WPLC2P83	26w PL-C 2 Pin Col 83
Std	26WPLC2P84	26w PL-C 2 Pin Col 84
Std	10WPLC4P83	10w PL-C 4 Pin Col 83
Std	10WPLC4P84	10w PL-C 4 Pin Col 84
Std	13WPLC4P83	13w PL-C 4 Pin Col 83
Std	13WPLC4P84	13w PL-C 4 Pin Col 84
Std	18WPLC4P83	18w PL-C 4 Pin Col 83
Std	18WPLC4P84	18w PL-C 4 Pin Col 84
Std	26WPLC4P83	26w PL-C 4 Pin Col 83
Std	26WPLC4P84	26w PL-C 4 Pin Col 84
Std	18WPLL4P83	18w PL-L 4 Pin Col 83
Std	18WPLL4P84	18w PL-L 4 Pin Col 84
Std	24WPLL4P83	24w PL-L 4 Pin Col 83
Std	24WPLL4P84	24w PL-L 4 Pin Col 84
Std	36WPLL4P83	36w PL-L 4 Pin Col 83
Std	36WPLL4P84	36w PL-L 4 Pin Col 84
Std	40WPLL4P83	40w PL-L 4 Pin Col 83
Std	40WPLL4P84	40w PL-L 4 Pin Col 84
Std	55WPLL4P83	55w PL-L 4 Pin Col 83
Std	55WPLL4P84	55w PL-L 4 Pin Col 84
Std	5WPLS2P83	5w PL-S 2 Pin Col 83
Std	5WPLS2P84	5w PL-S 2 Pin Col 84
Std	7WPLS2P83	7w PL-S 2 Pin Col 83
Std	7WPLS2P84	7w PL-S 2 Pin Col 84
Std	9WPLS2P83	9w PL-S 2 Pin Col 83
Std	9WPLS2P84	9w PL-S 2 Pin Col 84
Std	11WPLS2P83	11w PL-S 2 Pin Col 83
Std	11WPLS2P84	11w PL-S 2 Pin Col 84

Length	Stock Code	Description
Std	18WPLT2P83	18w PL-T 2 Pin Col 83
Std	18WPLT2P84	18w PL-T 2 Pin Col 84
Std	18WPLT4P83	18w PL-T 4 Pin Col 83
Std	18WPLT4P84	18w PL-T 4 Pin Col 84
Std	32WPLT4P83	32w PL-T 4 Pin Col 83
Std	32WPLT4P84	32w PL-T 4 Pin Col 84
Std	42WPLT4P83	42w PL-T 4 Pin Col 83
Std	42WPLT4P84	42w PL-T 4 Pin Col 84
Std	11WPLE-C827BC/ES	11w PLE-C Col 827 BC/ES
Std	14WPLE-C827BC/ES	14w PLE-C Col 827 BC/ES
Std	18WPLE-C827BC/ES	18w PLE-C Col 827 BC/ES



**For more information please contact one of our Sales Team on:**

Tel: +44 (0) 1842 763752

Fax: +44 (0) 1842 765252

Email: [sales@fotolec.com](mailto:sales@fotolec.com)

[www.glassguard.co.uk](http://www.glassguard.co.uk)



## Coated Fragment Retention Lamps by FOTOLEC TECHNOLOGIES LTD

- All GlassGuard BlackBand® Fluorescent Lamps Meet IEC61549 Fragment Retention Lamp Standard & All EUP Regulations
- All Lamps Suitable For Open & Enclosed Fixture Operation
- Exclusive Single BlackBand® Ring Optimises Safety by Enabling Remote Lamp Identification & Compliance
- Achieves H.A.C.C.P Compliance Quickly & Easily to a High Standard
- Creates a Glass Free Environment Protecting Product, Profits & Personnel
- Long Life 20,000 Hour Protection Providing Significant Client Savings Through Cost of Ownership
- Lamp & Coating Fully Recyclable

GlassGuard BlackBand® and the Coated Outside logo are Registered Trademarks of Fotolec Technologies Ltd

Fotolec Technologies Ltd  
5 Baird Way  
Fison Way Industrial Estate  
Thetford, Norfolk, IP24 1JA  
United Kingdom

Tel: +44 (0) 1842 763752  
Fax: +44 (0) 1842 765252  
Email: [sales@fotolec.com](mailto:sales@fotolec.com)  
[www.glassguard.co.uk](http://www.glassguard.co.uk)