

Features

- Max 99999 hours
- Digital display to see count number
- 7 displays
- 160-240V AC and 24V AC-DC operating

RS PRO Counters

RS Stock No.: 0434511



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Hour meters are designed to calculate the total operating time of an electrical machine.*
- *To see a load total working time hour*

General Specifications

Product type	Counters
Supply voltage	External
Operating voltage	160-240V AC , 24V AC-DC
Mode of operation	Counting
Max voltage	250V AC
Function measured	Sec, min, hour
True RMS	YES
Display type	Display screen
Operating temperature	-20, +55
Storage temperature	-30, +80
Surge protection	YES
Mounting type	Assembled on the panel
Connection type	Terminal
Monitoring application	Time
Electrical phase	L+N
Time range	99999 hours
Count mode	Sec, min, hour
Display type	7 segments led
Number of digits	7 digits
Cut-out size	72X72
Reset mode	No reset
Input type	AC-DC
Function	counter
Connection type	Cable to terminal

Mechanical Specifications

Width	32 mm
Length	72 mm
Height	72 mm
Weight	< 60 gr

Electrical Specifications

Operating voltage	160-240V AC
Frequency	50/60 Hz
Safety Category voltage	CATII
Cable diameter	2,5mm

Protection Category

IP rating	IP20 body
-----------	-----------

Approvals

Compliance/Certifications	CE-UKCA
Hazardous Area Certification	ROHS-3

Wiring Diagram

