

Technical sheet


TPZ1100CV

Green flexible bollard H 1130/930mm-d.80mm-to embed- cylindrical head

Flexible shape memory green post, 80 mm diameter, cylindrical head, prevents damage to vehicles. In case of impact, the bollard deforms to return to its initial shape and without breaking the sealing or fixing. Resistant to tearing, pulling, and breaking. Used for separating and protecting different areas in the city and parking lots. Height 1000mm. To be fixed directly in the ground. Fixings not included. Multiple options available: chain ring, reflective tape, fixing, specific color.









Customs code	3926909790
EAN	3321360026675

Color : Green (RAL6005)

Material : Polyurethane

Specifications :

- Flexible memory-shaped bollard designed to prevent vehicle damage.
- In case of impact, the bollard deforms to its initial shape without breaking the anchoring or fixation.
- Resistant to tearing, pulling, and breaking.
- Various options available: head type, PMR standard, to be fixed or anchored, removable box, with or without reflective tape...

Height (mm)	Diameter (mm)	Total height (mm)	Type of post	Net weight (kg)
930	80	1130	to seal	2,70

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com