

Product data sheet

Specifications



Floor standing encl.polyester vers.PLAZT w/open plinth+canopy 1500x1000x320 IP44

NSYPLAZT15103G

Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLAZT
Nominal height	1500 mm
Nominal width	1000 mm
Nominal depth	320 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy 1 plinth

Complementary

Body type	Open top and bottom part assembled with side parts
Door type	Plain front
Number of doors	2 door(s)
Door opening side	Right and left (180 °)
Lock type	4 points lock, handle with 5 mm double bar insert
Accessibility for operation	Rear Bottom Front Top
Removable parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	Veritas
Electrical insulation class	Class II

Environment

IP degree of protection	IP44 conforming to IEC 60529 (with plinth type open bottom part and ventilated canopy)
IK degree of protection	IK10 conforming to IEC 62262 (plain door)
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for storage	-35...90 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	62.435 kg
Package 1 Height	156.0 cm
Package 1 width	103.0 cm
Package 1 Length	38.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile