

## Technical data sheet

Article number:  
118-00149

**T50ROS**



|                                    |  |
|------------------------------------|--|
| <b>Product Group</b>               | Cable ties made from post-industrial recycled polyamide 6.6  |
| <b>Product Family</b>              | OS-Series in PA66HIRHS(REC) black  |
| <b>Material</b>                    | Polyamide 6.6 recycled, high impact modified, heat stabilised (PA66HIRHS(REC))   |
| <b>Colour</b>                      | Black (BK)   |
| <b>Application Tool</b>            | ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP |
| <b>Bundle Ø max.</b>               | 50.0 mm  |
| <b>Bundle Ø min.</b>               | 1.6 mm   |
| <b>Halogen-free</b>                | Yes  |
| <b>Height (H)</b>                  | 1.3 mm   |
| <b>Length (L)</b>                  | 203.2 mm   |
| <b>Min.Tensile Strength</b>        | 225 N  |
| <b>Operating Temperature</b>       | -40 °C to +105 °C  |
| <b>Package Content packed in</b>   | bag  |
| <b>Pack Cont.</b>                  | 100 pcs.   |
| <b>Releasable Closure (Yes/No)</b> | No   |
| <b>Toothing (Serration)</b>        | Outside Serrated   |
| <b>Variant</b>                     | Outside Serrated   |
| <b>Weight/Unit</b>                 | 0.00126 kg   |
| <b>Width (W)</b>                   | 4.6 mm   |

