

## **FEATURES**

- Application : Plumbing, Water
- Handle clearly shows ball position
- Silicone-free lubricant on all seals
- Chrome plated brass ball for longer life
- No metal-to-metal moving parts

# RS PRO Brass High Pressure Ball Valve 1/2 in BSPP 2 Way

RS Stock No.: 733-5224



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



# **Product Description**

RS PRO range of brass manual ball valves. Manual ball valves are used to operate shut off valves which control water flow and pressure. These quarter turn brass full bore ball valves have a t-handle and are suitable for high temperature hot water services in domestic, commercial and industrial applications.

733-5215 - T handle ball valve 3/8 inch M-F

733-5224 - T handle ball valve 1/2 inch M-F

733-5227 - T handle ball valve 3/4 inch M-F

733-5221 - T handle ball valve 1 inch M-F

733-5211 - T handle ball valve 1/4 inch M-F

#### **General Specifications**

Threaded Connection	1/2 in BSPP
Attachment Type	Threaded
Body Material	Brass
Thread Size	1/2in
Safe For Use With	Air, Oil, Steam, Water
Туре	2 Way
Application	Heating systems; Water treatment; Liquid flow control

#### **Mechanical Specifications**

Connection Size	12.7mm	

### **Operation Environment Specifications**

Working Temperature	-20°C to 170°C
Maximum Working Pressure	40 bar



# **Approvals**

Compliance/Certifications

WRAS (UK), GOST-R (Russia), Expert Conclusion (Russia), EAC Conforming (Russia), UkrSepro (Ukraine), RoHS Compliant








	PART DESCRIPTION	Q.TY	MATERIAL
1	Nickel plated body (external nickel plated, unplated inside up to 2")	1	CW617N
2	Seat	2	PTFE
3	Chrome plated ball	1	CW617N
4	Nickel plated end-cap (external nickel plated, unplated inside up to 2")	1	CW617N
5	Nickel plated stem O-ring design	1	CW617N
6	Geomet® nut	1	CB4FF
7	O-Ring	2	FPM
8	Red PVC coated Geomet® steel handle	1	DD11

Code	890B00	890C00	890D00	890E00	890F00	890G00	890H00	890100	390L00	B90M00	890N00
D (inch)	1/4	3/8	1/2	3/4	1	1 1/4	11/2	2	21/2	3	4
DN (mm)	8	10	15	20	25	32	40	50	65	80	100
I (mm)	9	9	11	12	14	15	17	19	22	25	29
L (mm)	39	39	50	54	67	77	90	106	136	157	191
G (mm)	19,5	19,5	25	27	33,5	38,5	45	53	68	78.5	96,5
A (mm)	82	82	100	120	120	158	158	158	255	255	255
H (mm)	38	38	43	50	54	73	79	86	132	140	154
CH (mm)	20	20	25	31	38	48	54	66	85	99	125

#### Pressure-temperature chart



#### Pressure drop chart

