



E2E-X9B212 2M

Proximity sensor, inductive, nickel-brass, short body, M12, shielded, 9 mm, DC, 3-wire, PNP NC, 2 m cable

Specifications

Size	M12
Mounting type	Quasi-flush
Sensing distance	9 mm
Overall length of sensor	47.1 mm
Thread length	28 mm
Material housing	Brass, nickel plated
Output type	PNP
Operation mode	NC
Connection method	Cable
Cable specifications	PVC (oil-resistant)
Cable length	2 m
IO-Link function	✗
IO-Link baud rate	Not Applicable
Degree of protection (IP)	IP67/IP67G/IP69K

Accessories



Y92E-J12S18

Mounting Sleeves e-jig for M12 Prox

CAD Library



E2E NEXT Datasheet

EN PDF 40 MB



E2E(Q)- XB XC_premium_model Instruction Sheet

EN PDF 3.66 MB



IO-Link Series Brochure

EN PDF 6.41 MB