

Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)
- Available in Red, Black, Yellow, Blue, White and Silver

RS PRO Fire Sleeve Yellow 15m

RS Stock No.: 0733584



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

General Specifications

Part Number	Ordering Size (mm)
0731334	4
0733559	6
0733560	8
0733561	10
0733562	12
0733563	14
0733565	16
0733566	19
0733567	22
0733568	25
0733569	28
0733571	32
0733572	35
0733573	38
0733574	41
0733575	44
0733576	51
0733577	57
0733578	63
0733579	70
0733580	76
0733581	83
0733582	89
0733583	95
0733584	102
0733585	114
0733587	127
0733588	140
0733590	168
0733591	180
0733743	203

Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2