

## FEATURES

- **Nylon Material:** Provides excellent strength and flexibility for secure cable bundling
- **Non-Releasable Design:** Ensures a permanent and secure hold
- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **High Tensile Strength of 55 kg:** Capable of handling heavy-duty applications
- **Wide Operating Temperature Range:** Functions effectively from -40 °C to 85 °C, suitable for various environments
- **UL 94HB Fire Behaviour:** Meets safety standards for flammability
- **RoHS Compliant:** Environmentally friendly, adhering to safety regulations

## RS PRO 370mm Nylon Cable Tie, Non-Releasable

RS Stock No: 656-099



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

RS PRO offers a robust and reliable solution for cable management with its 370mm Nylon Cable Tie. Designed for securing and organising cables, this non-releasable tie is ideal for both industrial and domestic applications. Its high tensile strength ensures durability and long-lasting performance.

### General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	55 kg

### Protection Category

Fire Behaviour	UL 94HB
UV Resistant	Yes

### Mechanical Specifications

Length	370 mm
Material	Nylon
Maximum Bundle Diameter	101 mm
Width	7.6 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

### Approvals

Standards/Approvals	RoHS, UL94HB
---------------------	--------------