

TECHNICAL DATA

Version 4

AT6150 Polythene Vapour Barrier/Protection Tape

General Description

A polythene film, coated with a clear, aggressive, pressure sensitive adhesive.

- Easy unwind
- Flexible at low temperature
- Easy tear
- Water resistant
- Good abrasion resistance
- Conformable
- Non-corrosive adhesive
- Good tack



Technical Details

Typical Values

Thickness	0.11mm
Breaking Load	15 N/cm
Elongation	200%
Adhesion	
Steel	2.5 N/cm
Self	1.5 N/cm
RoHS compliant	Yes
Service Temperature	-5°C to +50°C
Application Temperature	0°C to +40°C
Storage Temperature	+12°C to +25°C

NOTE

Except where indicated otherwise, the figures stated are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The Company reserves the right to improve products and any change in specification will result in a re-issue of the relevant 'Technical Data Sheet'. Customers should satisfy themselves that the tape is suitable for their requirements whether after such modifications or otherwise. Please check that you have the latest issue of the 'Technical Data Sheet'. All slitting and length tolerances are to British Standards. Before use the customer is advised to consult the Health & Safety Data Sheet produced by the company for this product, which is available on request.

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.



AFERA

Association des Fabricants Européens de Rubans Auto-Adhésifs.

Adding more to adhesive tape

Registered in England No. 929843
Vat No. 115-6143-00

Advance Tapes International Limited
Westmoreland Avenue
Thurmaston
Leicester LE4 8PH
England

Tel. +44 (0)116 251 0191
Fax. +44 (0)116 265 2046
contact@advancetapes.com

www.advancetapes.com



Q05026