

910MQ/B

Bi-hex sockets



EN 60900



	art.	mm	Ø mm	L mm	Ø1 mm	A mm	g
009100616	910MQ-B 6	6	24	45	14	11	30
009100617	910MQ-B 7	7	24	45	15	11	30
009100618	910MQ-B 8	8	24	45	16	11	30
009100619	910MQ-B 9	9	24	45	17	11	35
009100620	910MQ-B 10	10	24	45	19	11	35
009100621	910MQ-B 11	11	24	45	20	11	35
009100622	910MQ-B 12	12	24	45	24	11	40
009100623	910MQ-B 13	13	24	45	24	11	40
009100624	910MQ-B 14	14	24	45	25	13	40
009100625	910MQ-B 15	15	24	45	27	13	45
009100626	910MQ-B 16	16	24	45	27,5	13	45
009100627	910MQ-B 17	17	24	45	30	13	50
009100628	910MQ-B 18	18	24	45	31	13	50
009100629	910MQ-B 19	19	24	45	32	13	60