

**CAB CAB P 1008030 T**



Sample photo

**Order symbol:** CAB P 1008030 T  
**Product nbr:** 8104009  
**Description:** Polyester cabinet  
**Remarks:** Glazed door

**EAN:** 6418074050120  
**EI. number:**  
 Finland: 3438124  
 Electric No. 8212018222  
 Denmark:  
 Electric No. Sweden: 2539815

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with transport and plastic key.

Dimensions:	Length	Width	Height	Accessories:	
<b>mm:</b>	1035	835	300	FP 10080-D	Swing door/Front plate
<b>inch:</b>	40.7	32.9	11.8	MB CAB	Swing door kit
<b>Materials:</b>				MPP 10080	Mounting Plate
<b>Material:</b>	Polyester			MPX 10080	Mounting Plate
<b>Base colour:</b>	RAL 7035 -light grey			MF10080	Mounting Frame with DIN-rails
<b>Cover colour:</b>	RAL 7035 -light grey			FP 10080-5x36	Front Plate with DIN openings
<b>Gasket material:</b>	Polyurethane			<b>Rating:</b>	
<b>Temperatures:</b>				Ingress Protection (EN 60529): IP66	
<b>Temperature °C (short term):</b>	-50 ... 160 °C			Impact Resistance (EN 62262): IK07	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Electrical insulation: Totally insulated	
<b>Temperature °F (short term):</b>	-60 ... 320 °F			UV resistance: UL 508	
<b>Temperature °F (continuous):</b>	-40 ... 176 °F			Flammability Rating: UL 94 HB	
<b>Accessories:</b>				Glow Wire Test (IEC 695-2-1) °C: 960	
MP 10080	Mounting plate			<b>Certificates:</b>	
				Gost R	

