



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-1393143-1 27E637=SOCKET,R10,4POLE,PCB,.210	TE Part # 4-1393143-9 27E630=SOCKET,R10,6POLE,PCB,.180	TE Part # 1-1393143-1 27E128=SOCKET,R10,10,PC,PHEN	TE Part # 1-1393143-2 27E129=SOCKET,R10,16,PC,PHEN



TE Part # 2-1393143-5
27E213=SOCKET,R10,16,PC,PHEN



TE Part # 2-1393143-4
27E212=SOCKET,R10,10,PC,PHEN



TE Part # 3-1393143-1
27E271=SOCKET,R10,22,PC,PHEN



TE Part # 2-1393143-1
27E193=SOCKET,R10,11,PC,PHEN



TE Part # 5-1393143-0
27E636=SOCKET,R10,2POLE,PCB,.210



TE Part # 1-1393143-3
27E130=SOCKET,R10,22,PC,PHEN



TE Part # 2-1393143-2
27E194=SOCKET,R10,16,PC,PHEN



TE Part # 3-1393143-6
27E342=SOCKET,R10,2POLE,PCB,.180



TE Part # 4-1393143-8
27E629=SOCKET,R10,4POLE,PCB,.180

Customers Also Bought



TE Part #1648183-1
291-10-01100=SA CONN,PIN



TE Part #CAT-104MTA-NTPNR
MTA Receptacle: Nylon, Tin Plated, 2.54 mm




TE Part #1-1393767-5
R10-E2X2-V700=R10




TE Part #1648186-1
292-10-01100=SA CONN,SKT



TE Part #3-1879355-6
RR03 5% 120K AMMO



TE Part #CAT-104MTA-NGPNR
Nylon Gold Plated Receptacle: 2.54 mm, no Mating Alignment



TE Part #284392-4
TERMI-BLOK PCB SIDE ENTRY STAC



TE Part #4-1393143-8
27E629=SOCKET,R10,4POLE,PCB,.180

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1393159-0_3.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1393159-0_3.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1393159-0_3.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

R10 Sockets & Accessories

English