

Product data sheet

Power tools for trade & industry

Cordless Threaded Rod Cutter

PRO GGC 18V-12



The convenient, spark-free cutter for threaded rods

The most important data

Part Number 0 601 9M8 001

Technical data

#t-productdetailpage_tools.technical-data.bi.
additional-data}

Cutting capacities steel	M6 - M12
Cutting capacities stainless steel	M6 - M10
Closest cut-off	37 mm
Work light	+

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Convenient working thanks to burr-free cuts for mounting nuts without rework
- Ideal for mobile and stationary jobs thanks to ideally balanced design
- High protection with spark-free cutting ensured by scissor mechanism

