

# MPR16 Plastic



Products Low Voltage Products and Systems Industrial Plugs and Sockets Modular Combination Boxes

## General Information

<b>Extended Product Type:</b>	MPR16 Plastic
<b>Product ID:</b>	2CMA168997R1000
<b>EAN:</b>	7392696689977
<b>Catalog Description:</b>	Modular Combi Plastic, 16A, 1x3P+N+E, 250x300x160, 2x10/16A, IP44
<b>Long Description:</b>	Modular Combi 16 A, MPR16, Plastic

## Additional Information

<b>Additional Information:</b>	Cable entry,4 knock-outs at the top,suitable for 2xØ40mm and 2xØ25mm,at the bottom 3xØ47mm
<b>Cable Cross-Section:</b>	16 mm²
<b>Cable Entry Position:</b>	Cable entry,4 knock-outs at the top,suitable for 2xØ40mm and 2xØ25mm,at the bottom 3xØ47mm
<b>Color:</b>	Grey
<b>Country of Origin:</b>	Czech Republic (CZ)
<b>Customs Tariff Number:</b>	85366990
<b>Data Sheet, Technical Information:</b>	2CMC700014C0008
<b>Declaration:</b>	2CMC700005D0004
<b>Declaration of Conformity - CE:</b>	2CMC700005D0004
<b>Degree of Protection:</b>	IP44
<b>E-nummer:</b>	2466345
<b>EAN:</b>	7392696689977
<b>ETIM 4:</b>	EC000379 - CEE socket outlet combination
<b>ETIM 5:</b>	EC000379 - CEE socket outlet combination
<b>ETIM 6:</b>	EC000379 - CEE socket outlet combination
<b>Enclosure Material:</b>	Plastic
<b>Environmental Information:</b>	2CMC700001D0002
<b>Function:</b>	Combination box
<b>Gross Weight:</b>	3.32 kg
<b>Housing Material:</b>	Thermoplastic (PBT)
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Instructions and Manuals:</b>	2CMC711001M0201
<b>Invoice Description:</b>	Ind. P&S#MPR16
<b>Minimum Order Quantity:</b>	1 piece
<b>Number of Poles:</b>	5
<b>Number of RCD 30mA:</b>	1
<b>Number of RCDs:</b>	1
<b>Number of Schuko Outlets:</b>	2
<b>Object Classification Code:</b>	2CMT005069
<b>Package Level 1 EAN:</b>	7392696689977
<b>Package Level 1 Gross Weight:</b>	3.32 kg
<b>Package Level 1 Height:</b>	490 mm
<b>Package Level 1 Length:</b>	270 mm
<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	210 mm
<b>Product Main Type:</b>	MPR

<b>Product Name:</b>	Modular Combi
<b>Product Net Depth:</b>	154 mm
<b>Product Net Height:</b>	154 mm
<b>Product Net Length:</b>	360 mm
<b>Product Net Weight:</b>	3 kg
<b>Product Net Width:</b>	250 mm
<b>Protection Type:</b>	Splashproof
<b>Rated Current (I<sub>n</sub>):</b>	16 A
<b>Rated Residual Current:</b>	30mA
<b>Rated Voltage (U<sub>r</sub>):</b>	346 ... 415 V
<b>RoHS Date:</b>	L23
<b>RoHS Information:</b>	2CMC700057D0001
<b>RoHS Status:</b>	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	Modular Combi Plastic, 16A, 1x3P+N+E, 250x300x160, 2x10/16A, IP44
<b>Size:</b>	360X250X154
<b>Standards:</b>	IEC 61439-1 IEC 61439-2
<b>Suitable For:</b>	MPR16 Modular Combi Plastic
<b>Suitable for Product Class:</b>	Industrial Plugs and Sockets
<b>UNSPSC:</b>	39120000
<b>Clock Position Of Grounding Contact:</b>	6 hour

