
Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20SBKO06EVX
BODY MATERIAL: Stainless Steel 316L
COUPLING HALF: Plug
CONNECTION TYPE: Tube
FUNCTION: Double Shut-Off
CONNECTION SIZE: 4x6 MM

PRODUCT OVERVIEW

Parker’s Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:
- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

DIAMETER	2.7 mm (nominal)
MINIMUM OPERATING TEMPERATURE	-15 °C
APPLICATION	Industrial Machinery
CONNECTION TYPE	Tube With hose nut, without spring guard
FOR FLUID TYPE	Chemicals (Paints, solvents, lubricants)
INDUSTRY	Healthcare & Life Sciences
CONNECTION SIZE	4x6 mm
APPLICATION	Energy Management
FUNCTION	Double Shut-Off
FOR FLUID TYPE	Water (Industrial, drinking, treated water)
INTERCHANGE TYPE	European Profile
MAXIMUM OPERATING TEMPERATURE	392 °F
VALVE INCLUDED	Yes
PRODUCT SERIES	Series 20
MINIMUM OPERATING TEMPERATURE	5 °F
APPLICATION	Medical
PRODUCT TYPE	Pneumatic Quick Couplings
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
BRAND	Parker

MAXIMUM OPERATING TEMPERATURE	200 °C
MAXIMUM OPERATING PRESSURE	507 psi
TECHNOLOGY	Fluid & Gas Handling
FLOW RATE	1.2 L/min (water)
MAXIMUM OPERATING PRESSURE	35 bar
APPLICATION	Food & Beverages
APPLICATION	Pharma
WEIGHT	0.01 kg
INDUSTRY	Electronics
BRAND	Rectus
COMPATIBLE FITTING	Series 20 Coupler
SLEEVE MATERIAL	Without Sleeve
INDUSTRY	General Industrial
LENGTH	36 mm
APPLICATION	Electronics
HEX SIZE	9 mm (external)
VALVE TYPE	Standard Valve
PLATING TYPE	Without Surface Treatment
DIVISION	Low Pressure Connectors Europe Division
FLOW RATE	130 L/min (air)
DIVISION	Low Pressure Connectors Europe Division
TECHNOLOGY	Pneumatics
BODY MATERIAL	Stainless Steel 316L
QUANTITY PER BOX	2.0
SEAL MATERIAL	FKM
OPERATION TYPE	No Sleeve

COUPLING HALF	Plug
REGION OF ORIGIN	Germany
PRODUCT STYLE	Quick Connect