

uvex

**SAFETY
EYEWEAR**

22.11.2017

Product Datasheet model i-vo 9160 265



UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth

Product characteristics	<ul style="list-style-type: none">• fashionable safety spectacles with adjustable side arms• reliable protection provided by its perfect fit: multi-level side arm inclination and different side arm lengths allow the wearer to adjust the spectacles to suit their own face shape• soft, uvex quattroflex arms and soft components at the nose and forehead ensure a comfortable, pressure-free fit• the shape of the lenses ensures unrestricted peripheral vision
Technical details	
Frame	Front piece
Material	TPU/TPE
Colour	blue/orange

Material	Side piece
Features	PA
Colour	5 position length adjustability
	blue
Material	Temple
Features	PBT+PC/TPE
Colour	quattroflex temple
	blue/orange
Manufacturer's ID code	Marking
Applicable EN norm	W
Impact resistance	166
Resistance to high speed particles at extremes of temperat.	F (45 m/s)
Conformity symbol	T
	CE
Lens	
Material	PC
Thickness	3 mm
Coating	supravisio excellence
Colour	clear
UV protection	UV 400

	Marking
Filter	2C-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat	T
Surface resistance to fine particles	K
Antifog	N
Tested acc. to DIN	DIN
Conformity symbol	CE
Miscellaneous	
Weight	33 g
Packing	5 spectacles per box 200 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II