

278700**Manual bending tool set**

Code	ETIM
1589865	EC011119
EAN	UNSPSC
4017981278706	27-11-25-01
Country of origin	eCl@ss
Germany	21-04-16-03
Customs tariff number	
82055980	

**Article description**

- Sizes from 20 to 25 mm Ø to 180°
- For precision steel pipes EN 10305-3 (DIN 2394), hydraulic pipes EN 10305-1 (DIN 2391) with 1.5 - 2.5 mm wall thicknesses, composite pipes up to 25 mm as well as bendable stainless steel pipes with 1.5 - 2.0 mm wall thicknesses
- For clamping in a vice
- With 3 aluminium bending formers for pipes with Ø 20, 22, 25 mm
- Painted blue, with black plastic handle

Article parts list

1 basic tool body 20-25 mm No. 278770,1 bending lever 20-25 mm No. 278781,3 aluminium bending formers for pipes with Ø 20, 22, 25 mm

Article information

Contents [Qty of pieces] 1 Net weight [kg] 13.04 kg