

Natural rubber-coated heavy-duty gloves, with a 100% cotton liner for optimal comfort

- **Elevated comfort:** Designed for heavyweight applications, AlphaTec® 62-401 protective gloves' cotton lining provides excellent thermal insulation in hot and cold conditions, for assured comfort with intensive use
- **Enhanced grip:** These liquid-proof latex gloves feature a wrinkled finish, ensuring superb grip performance in wet and dry conditions
- **Advanced ergonomics:** AlphaTec® 62-401 hand protection gloves are ergonomically designed to provide wearers with an optimal fit and excellent flexibility
- **Food handling compliance:** Ideal food safety gloves, they meet relevant FDA food handling requirements
- **Assured quality:** In addition, AlphaTec® 62-401 industrial gloves achieve an AQL of 1.5

Industries

- Automotive Aftermarket
- Food Processing
- Glass manufacturing
- Machinery and Equipment
- Construction

Applications

- Glass repair and replacement
- Deboning
- Steaming, frying and roasting



Previously known as: VersaTouch® 62-401

Key Features

- **100% cotton liner:** Optimal comfort and excellent thermal insulation*
- **Wrinkled finish:** Safer handling in wet and dry work environments
- **Ergonomic fit:** For form-fitting, comfortable and flexible work gloves

*protecting wearers from hot or cold temperatures



Vulcanization Chemical Accelerators

- Natural rubber proteins
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards

ANSI/ISEA 105-2024



0493

EN388: 2016



3131B

EN 407



X2XXXX

EN 407



X2XXXX

EN 511



011

EN ISO 374-1:2016 Type A



AKLMPT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 62-401	Liner Material: Cotton Jersey Coating Material: Natural Rubber Latex	7, 8, 9, 10, 11	320 / 12.6	Blue	6 pairs per bag; 8 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.