



verso maintenance trolley with 7 drawers / cupboard & top tray with mat. Featuring a robust, fully welded steel housing with double, independent, storage sections, push - pull handles, 100% extension drawers with drawer blocking and 125mm diameter castors. Drawer configuration: 6x 100mm, 1x 125mm (50 kg U.D.L.) and cupboard section with single, reinforced, door and 1 galvanised steel shelf (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 7016 anthracite grey. WxDxH: 1300x550x965mm

Breite [mm]: 1300  
Tiefe [mm]: 550  
Höhe [mm]: 965  
Bruttogewicht [kg]: 118.75  
EAN-Code: 5039350148631  
Zolltarifnummer UK: 94032080  
Ursprungsland: GB

## Produkteigenschaften

|                      |                 |
|----------------------|-----------------|
| Product surface      | Powder coated   |
| Product material     | Sheet steel     |
| Main colour          | Anthracite grey |
| Main RAL colour      | RAL 7016        |
| Secondary colour     | Light grey      |
| Secondary RAL colour | RAL 7035        |

## Artikelbeschreibungen

|               |       |
|---------------|-------|
| Product brand | verso |
|---------------|-------|

## Schubladen

|                           |     |
|---------------------------|-----|
| Number of drawers         | 7   |
| Drawer load capacity [kg] | 50  |
| Drawer height 1 [mm]      | 100 |
| Drawer height 2 [mm]      | 100 |
| Drawer height 3 [mm]      | 100 |

|                      |     |
|----------------------|-----|
| Drawer height 4 [mm] | 100 |
| Drawer height 5 [mm] | 100 |
| Drawer height 6 [mm] | 100 |
| Drawer height 7 [mm] | 125 |

## Schrank, Gehäuse, Werkbank und EAP

|                          |                  |
|--------------------------|------------------|
| Worktop/housing top type | Top tray and mat |
| Shelf load capacity [kg] | 75               |
| Door type                | Plain            |
| Door height 1 [mm]       | 725              |