



RLS4FC

4 pole loudspeaker cable connector with latch lock, chuck and bushing, bulk packed, to be ordered in multiples of 100 pcs.

Article Variations

Article Name	Details	Packaging
RLS4FC	4 pole loudspeaker cable connector	BULK
RLS4FC-D	4 pole loudspeaker cable connector	BULK

Technical Information

Product

Title	RLS4FC
Connection Type	Loudspeaker Connectors

Electrical

Contact resistance	≤ 5 mΩ (after lifetime)
Dielectric strength	4 kVdc (peak)
Insulation resistance	> 1 GΩ (after dampheat test)
Rated current per contact	30 A
Rated voltage	250 V (insulation)
Attention	Shall NOT be used as an AC mains connector!

Mechanical

Cable O.D.	6 - 10 mm
Lifetime	> 1000 mating cycles
Wiresize	4 mm ²
Wiresize	12 AWG

Environmental

Temperature range	-30 °C to +80 °C
--------------------------	------------------