

FMHT83006-0

SERRE-JOINT HYBRIDE 300MM FATMAX

3253560830069



Product Description:

DESIGNED TO PROVIDE USERS WITH STRENGTH, SPEED AND EASE OF USE - Offers the power of a screw clamp combined with the ease of use and speed of a one-handed clamp - 136KG OF INITIAL CLAMPING FORCE obtained with the trigger handle - 374KG OF CLAMPING FORCE obtained with the screw grip (can be used with a wrench to apply more force) - BUILT-IN COUPLER to combine two clamps for more length - CLAMPING MECHANISM QUICK CHANGE for quick, tool-free conversion to a spreader • V-shaped jaws and pads for secure clamping of irregularly shaped objects and pipes • Metal jaws and steel bar prevent bending and flexing under pressure, while increasing durability

Product features and benefits:

- FAST-TIGHTENING- Using the trigger handle, quickly get up to 136kg of clamping force CLAMPING FORCE - Using the screw-in handle, get
- and maintain up to 374kg of clamping force EASY CLAMPING - Use a wrench to help tighten the handle to the
-
- ADAPTABLE screws - To have more length, combine 2 clamps
-
- with the built-in coupler CONVENIENT - Easily convert the clamp into a spreader with the
- ROBUST Quick Reversing Mechanism - Metal jaws and steel bar
- prevent bending and flexing under pressure, while increasing the
-
- VERSATILE DURABILITY - V-shaped jaws and pads for secure
- clamping of irregularly shaped objects and pipes

Product Warranty:

This product is covered by the legal warranty

Specifications techniques :

- Clamping power: 374 Kg
- Clamping force: 374 Kg
- Jaw depth: 45 mm
- Spacing capacity: 790 mm
- Throat Depth: 80 mm Maximum Jaw
- Opening: 610 mm
-
- Shaft thickness: 6 mm Maximum
- clamping force: 374 Kg
- Shank length: 800 mm
- Jaw width: 26 mm Average clamping
- force: 136 Kg

