

1" TORQUE WRENCH PLUS 300 - 1500 NM



- 1" torque wrench
- $\pm 4\%$ accuracy
- 72-teeth ratchet mechanism compliant with DIN 3122
- Twist reverse and quick-release button for socket changes
- 5-degree swing arc for precise adjustments in confined spaces
- Locking device to prevent accidental torque setting changes
- Clear Nm scale for quick and reliable settings
- Ergonomic bi-material handle with hand placement markings
- Delivered in a durable storage case
- Individually tested to ISO 6789 standards with unique serial number and Declaration of Conformance

The TengTools 1192P1500 torque wrench with 1" square drive has a torque range of 300–1500 Nm with an accuracy of $\pm 4\%$ and is intended for professional users and large-scale industrial applications such as assembling heavy machinery or maintaining aircraft equipment. The 72-teeth ratchet mechanism is designed according to DIN 3122 with a twist reverse and quick-release button for sockets and socket accessories. The ratchet mechanism is constructed for clockwise fastening of right-hand threads and has a 5-degree swing arc, allowing precise adjustments even in confined spaces. The click-type mechanism provides an audible and tactile signal when the required torque is reached, preventing over-torquing. The tool is equipped with a locking device that prevents the selected torque setting from being accidentally changed. An easy-to-read Nm scale enables quick and reliable setting for efficient use. The ergonomic and non-slip bi-material handle has markings indicating where to place the hand for proper force application. The tool is delivered in a durable storage case for easy transport. Each torque wrench is assigned a unique number and individually tested to comply with ISO 6789 standards and comes with a 'Declaration of Conformance' for guaranteed accuracy.

General information

Country of origin: Taiwan
Barcode: 5020385034044
Tariff code Europe: 8204120000
ECCN US: EAR99
ETIM: EC002132
UNSPSC: 27111715

Features

1"

Attributes

Product type: Torque Wrenches
Drive: 1"
Number of teeth: 72
Range: 300-1500 Nm
Scale resolution: 10
Accuracy: $\pm 4\%$
Calibration certificate: Factory
Reverse direction: Twist
Preset: No
Angular gauge: No
Digital: No
Bi-directional: No
Mechanism: Click
Tethering facility: No

Dimensions

Net weight (g): 11550
Width (mm): 84
Length: 1755 mm

Technical changes and errors may occur. 04-02-2025 09:18

DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
 441 39 Alingsås,
 Sweden