

Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	3P + N
[I <sub>th</sub> ] conventional free air thermal current	25 A
I <sup>2</sup> t on activation	200000 A².s
Number of cables	4 cable(s) 4 mm² at 105 °C
Width	54 mm
Height	190 mm
Depth	61 mm





Complementary

[U <sub>i</sub> ] rated insulation voltage	690 V conforming to IEC 60439-1
9 mm pitches	6
Net weight	0.23 kg

Environment

Standards	IEC 60439
Product certifications	UL[RETURN]LROS (Lloyds register of shipping)[RETURN]CSA[RETURN]DNV

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.