

DYMO®

LW

LabelWriter™ 450 Turbo



HIGH-SPEED LABEL PRINTER FOR PC AND MAC®

- Save time - print up to 71 labels per minute*
- Label, mail, and file smarter directly from text in Microsoft® Word, Excel®, Outlook®, Google Contacts® and more with DYMO® Connect for Desktop Software
- Customize and print address, shipping, file folder and barcode labels, plus name badges and more - all from your PC or MAC®
- Create custom labels from 60+ label styles and layouts
- Direct Thermal printing technology - no ink or toner needed
- For even more features, download DYMO® Connect for Desktop Software

* 4-line address label



Single Unit Includes:

- LabelWriter 450 Turbo
- Address Labels Starter Roll
- Power Adapter
- Power Cable
- USB Cable
- Quick Start Guide
- 2 + 1 - Year Limited Warranty**



Quick Specs

Unit Dimensions (H x W x L)	16.3 x 26.9 x 14.0 mm
Weight	1.3 kg
Mac®/PC Compatible	Yes via DYMO® Connect for Desktop Software
Max Label Width	56 mm
Resolution	600 x 300 dpi
Printing System	Direct Thermal
Print Speed	71 labels/minute*
Barcodes	Yes
Power Source	Adapter Power Cable
Networking	Print Server Sold Separately
Country of Origin	China

Item Number	Description	Unit	Length (cm)	Width (cm)	Height (cm)	QTY	EAN	Customer Price
6868105	LabelWriter 450Turbo UK	Unit	14.0	26.9	16.3	1	3501170838860	

** +1 year if registered on the DYMO® website

LW Standard labels

Hassle-free labels for all your mailing, shipping and organizational needs.

Label Type	Description	Code #	Size (mm)	Rolls/Box	Labels/Roll	Adhesive	Material
Mailing	Standard Address Labels	Contact your RS Components team for availability.	28 x 89	2	130	Permanent	Paper
	Standard Address Labels	1794048	28 x 89	24	130	Permanent	Paper
	Standard Address Labels	1920478	28 x 89	12	130	Permanent	Paper
	Assorted Colour Labels	5418018	28 x 89	4	130	Permanent	Paper
	Large Address Labels	3298424	36 x 89	2	260	Permanent	Paper
	Large Address Labels	1794049	36 x 89	24	260	Permanent	Paper
	Large Address Labels	1920477	36 x 89	12	240	Permanent	Paper
	Large Address Labels	3415461	36 x 89	1	260	Permanent	Transparent Plastic
	Large Return Address Labels	5418080	25 x 54	1	500	Permanent	Paper
Shipping	Shipping / Name Badge Labels	3415483	54 x 101	1	220	Permanent	Paper
	High Capacity Shipping Labels	7951340	102 x 59	2	575	Permanent	Paper
	Shipping / Name Badge Labels	1920476	54 x 101	6	220	Permanent	Paper
	Shipping / Name Badge Labels	1794050	54 x 101	12	220	Permanent	Paper
	Extra Large Shipping Labels	6868114	104 x 159	1	220	Permanent	Paper
Multi-Purpose	Multi-Purpose Labels	5418024	13 x 25	1	1000	Removable	Paper
	Square Multi-Purpose Labels	7335851	25 x 25	1	750	Removable	Paper
	Multi-Purpose Labels	5418052	19 x 51	1	500	Removable	Paper
	Multi-Purpose Labels	5418030	32 x 57	1	1000	Removable	Paper
	Large Multi-Purpose Labels	3298430	54 x 70	1	320	Permanent	Paper
	Large Multi-Purpose Labels	1920479	32 x 57	6	1000	Permanent	Paper
	Large Multi-Purpose Labels	Contact your RS Components team for availability.	32 x 57	12	1000	Permanent	Paper
Specialty	Suspension File Labels	3298446	12 x 50	1	220	Permanent	Paper
	Small Lever Arch File Labels	3298452	38 x 190	1	110	Permanent	Paper
	Large Lever Arch File Labels	5418074	59 x 190	1	110	Permanent	Paper
	Small Name Badge Labels	5408213	41 x 89	1	300	Removable	Paper
	Appointment / Name Badge Cards	7335849	51 x 89	1	300	Non-adhesive	Paper

LW Durable Labels

Tear-resistant, coated polypropylene labels with extra-strength adhesive that withstand abrasion, common cleaners, and a wide range of temperatures-ideal for shelving, storage, and signage.



Water



Solvents



Oil



Textured Surfaces



Temperature
-18°C to 50°C

Label Type	Description	Code #	Size (mm)	Rolls/Box	Labels/Roll	Adhesive	Material
Durable	LW Durable Labels	1245851	25 x 89	1	350	Permanent	Coated Polypropylene
	LW Durable Labels	1245852	25 x 25	2	850	Permanent	Coated Polypropylene
	LW Durable Labels	1245853	32 x 57	1	800	Permanent	Coated Polypropylene
	LW Durable Labels	1245854	19 x 64	2	450	Permanent	Coated Polypropylene
	LW Durable Labels (4XL only)	1245855	104 x 159	1	200	Permanent	Coated Polypropylene
	LW Durable Labels	1245856	59 x 190	1	170	Permanent	Coated Polypropylene
	LW Durable Labels	1245857	59 x 102	1	300	Permanent	Coated Polypropylene
	LW Durable Labels	1245859	25 x 54	1	160	Permanent	Coated Polypropylene

The DYMO® high quality labels are made in Belgium



© 2019 Newell Brands

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

