




Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #1-776163-2
35POS, PIN DIA 1.3, HDR ASSY, 90DEG, COD 2




TE Part #8-640903-1
RECEPT, PIDG FASTON 22-18 250



TE Part #5788797-1
09 HTMSFL ASSY RA 318 (SL, BL)



TE Part #3-2176338-7
CRGCQ 0402 1M0 5%



TE Part #1-5103310-0
A/L LOW PRO HDR 50P RA BLACK




TE Part #1-2176230-1
3522 5R6 5% 3W




TE Part #1-1721150-5
ORWH-SH-124D1F,000



TE Part #5748027-1
25 PLUG SP/FMS (IN, SL)



TE Part #5536356-5
ASSY, PIN, EUROCARD, "C", LEAD-FREE, A&C, 64/9



TE Part #HPP845E032R5
I.C 21P RH/T PWM VERS.C1

Documents

Product Drawings
OZ-SS-124L1,200

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1649399-6_F.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1649399-6_F.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1649399-6_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



OZ_OZT Series Relay Data Sheet - English

English

Product Specifications

Product Specification

Japanese

Definitions General Purpose Relays

English