

PNOZ X7P 24VAC/DC 2n/o

777059



Safety relay (standalone), inputs: 1-channel wiring, outputs: 2 N/O, automatic/manual start, UB 24 V AC/DC, width: 22.5 mm, plug-in screw terminals, monitoring of E-STOP, safety gates.

Technical details

General data

Approval: CCC, CE, UKCA, cULus Listed, TÜV, EAC (Eurasian)

Technical data

Electrical data

Supply voltage (V): 24 - 24 V

Type of supply voltage U1: AC/DC

Power consumption AC: 3 VA

Power consumption DC: 1.5 W

Inputs

Number of inputs: 1

Semiconductor outputs

Number of semicond. outputs: 0

Relay outputs

Utilisation cat. AC/DC1 stand.: EN 60947-4-1

Voltage AC1 safety cont.: 240 V

Max. current AC1 safety cont.: 6 A

Voltage DC1 safety cont.: 24 V

Max. current DC1 safety cont.: 6 A

Utilisation cat. AC15/DC13sta.: EN 60947-5-1

Voltage AC15 safety cont.: 230 V

Max. current AC15 safety cont.:	5 A
Voltage DC13 safety cont.:	24 V
Safety contacts: AC at UL:	240 VAC G. P.
Safety contacts: pilot duty:	C300, R300
Relay contact material:	AgSnO ₂
Addit. contact details relay:	+ 0.2 µm Au
Environmental data	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	-10 - -10 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III / II
Pollution degree clear.&creep.:	2
Mechanical data	
Mounting position:	any
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Screw terminal
Terminal style:	plug-in
Flex. cond. c/s AWG info:	24 - 12 AWG
Height dimension:	94 mm
Width dimension:	22.5 mm
Depth dimension:	121 mm
Net weight:	190 g
Gross weight:	200 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU

RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85364900
UNSPSC 25:	39122331
EAN-Code:	4046548010121
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449
Volume:	0.301 dm ³

Optional accessories

374280

PNOZ X Set plug in screw terminals P1+P2

