

Features

- The head could rotate through 14 locking positions
- Able to reach areas inaccessible
- The overall length is adjustable to meet more demand
- Ideal tool for heavy-duty automotive or industrial work

RS PRO Extendable Indexing Pry Bar 20inch - 33inch Length

RS Stock No.: 0555928



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Extendable Indexing Pry Bar 20-inch – 33-inch Length

- Heads rotate 180° through 14 locking positions for unparalleled access and leverage. Compact design allows for work in tight spaces.
- Smooth head profile fits into low access, making quick work of pry jobs in cramped areas.
- The bar is solid with high strength and handle profile is anti-slip.
- The overall length is adjustable from 500mm to 830mm.
- Designed for demolition, repositioning equipment, industrial work or moving engines.

General Specifications

Size	20"-33"
Imperial or Metric	Imperial
Overall Length	500~830mm
Material	Alloy steel
Indexing	Yes
Finish	Black Phosphate

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Size	Overall Length
0555899	RS PRO	Indexing Pry Bar 8"	8"	200mm
0555902	RS PRO	Indexing Pry Bar 33"	33"	830mm
0555900	RS PRO	Indexing Pry Bar 24"	24"	600mm
0555927	RS PRO	Indexing Pry Bar 16"	16"	400mm
0555925	RS PRO	Indexing Pry Bar 10"	10"	250mm
0555903	RS PRO	Extendable Indexing Pry Bar 29"-48"	29"-48"	730~1200mm
0555928	RS PRO	Extendable Indexing Pry Bar 20"-33"	20"-33"	500~830mm