

rotronic

Datenblatt - Fiche technique - Data sheet



11.04.5655



**ROLINE Monitor-Kabel mit Ferritkern+DDC,
HD15 ST-BU, 6,0m**

**ROLINE Câble High Quality HD15 M/HD15 F
avec noyaux de ferrite + DDC, 6,0m**

**ROLINE High Quality VGA Cable
with Ferrite + DDC, HD15 M – HD15 F, 6 m**



Item no.	Length	Tolerance
11.04.5651	2000 mm	±30mm
11.04.5654	3000 mm	±30mm
11.04.5655	6000 mm	±50mm
11.04.5659	10000 mm	±100mm

NOTES:

- 1) P1&P2 COPPER FOIL 360° SHIELD
- 2) SHORT AND OPEN 100% TESTING
- 3) CONDUCTOR RESISTANCE 5Ω
- 4) INSULATION RESISTENCE 20MΩ
- 5) HI-POT: DC 250V

1	UL2919 28#3CO+28#9C+ADB (64%, AL-MG BRAID) OD:8.0MM BLACK 2000MM
2	HDB15M BLUE SOLDER TYPE TERMINAL GOLD FLASH WITH PIN 9 & 15
3	HDB15F BLUE SOLDER TYPE TERMINAL PLATED GOLD FLASH
4	OUTER JACKET PVC 45Pa BLACK
5	INNER JACKET PE

A	FIRST EDITION	SAN	2014/03/18
REV. ECR		C.N.	DATE
Item No.	11.04.5651, 11.04.5654, 11.04.5655, 11.04.5659		
ROLINE HQ VGA Cable, w/ferrite & DDC, HD 15M/F, black			
rotronic			
DIMENSIONS		TOLERANCE	
0.00 TO 30.00mm		±0.10mm	
30.01 TO 80.00mm		±0.13mm	
80.01 TO 150.00mm		±0.15mm	
150.01mm		±0.20mm	
MATERIAL		DR. SAN	APPD.
FINISH		PART NO.	
SCALE		SHEET 1/1	UNIT MM SIZE A4 REV. A