



Powder Free

Blue SynGuard Nitrile Gloves

Category III

Inco Medical is the Chinese leading manufacturer of medical disposable products and durable medical equipment and we have two major marketing centers in Los Angeles, USA and Shanghai, China, several sales offices in Canada, Malaysia and Germany as well as four factories separately in Shandong and Jiangsu. Our main businesses cover the R&D, production and sales of disposable medical gloves, wheelchairs, non-woven fabrics, hot/cold therapy, electrodes and other products. Since the establishment of 1990s, we have provided numerous high quality products and services to more than 100 countries and areas around the world.

RS Article	Material	Colour	Certifications	Size	Leakage Rating	Shelf Life	Quantity	Packaging Dimensions	Packaging Weight
2017879	Nitrile	Blue	EEN 374, EN 420, EN 455, EN 1186, EN 13485, EN 21171 CE marked to 93/42/EEC including 2017/47/EC CE Conformity also tested to EU 2017/745	Small	AQL1.5, 2.5, 4.0 optional	Usually 5 years	100 per box	230x125x60mm	400g
2017880				Medium					450g
2017881				Large					500g
2017882				X-Large					550g

Description

Comfortable, super soft flexible powder free nitrile gloves provide added safety applications. Designed with special nitrile formulation they feel and fit like latex and allow full range of motion and excellent flexibility to minimize stress and fatigue. They do not contain natural rubber latex and are excellent alternative for those suffering from Type I allergies.

Features

- 100% latex free-made from durable, puncture resistant, protein and powder- free nitrile, eliminates the Type I allergic reaction associated with natural rubber latex.
- Highly elastic and super soft.
- Rolled rim to facilitate easy donning.
- Designed to give a natural rubber-like feel.
- Food safe, suitable for handling fatty foods incl; cooking, olive and cod liver oil (Special Product).
- Textured in finger tips for enhanced grip in all situations.
- Protects against a wide variety of chemicals.

