



DDF 456 RJY CORDLESS DRILL SCREWDRIVER



DDF 456 RJY cordless drill screwdriver

Lithium-ion 18 volt

Execution

- 16 adjustable torque levels + adjustable drill setting
- Electronic switch for continuously variable speed control

Delivery

2 x batteries, DC18RC charger, size 2 MAKPAC

| | |
|---|-------------------|
| Model | DDF456RYJ |
| Motor design | 4 pole motor |
| Rechargeable battery/battery capacity | 1.5 Ah |
| Type of rechargeable battery/battery | Li-Ion |
| Max. drilling diameter in steel | 13 mm |
| Max. drilling diameter in wood | 38 mm |
| Idle speed 1st gear min./max. | 0-400 U/min(rpm) |
| Idle speed 2nd gear min./max. | 0-1500 U/min(rpm) |
| Max. torque for hard screwing application | 50 Nm |
| Max. torque for soft screwing application | 36 Nm |
| Weight | 1.7 kg |
| With working lights | Yes |
| With rubber-coated handle | Yes |
| Gross Weight | 4.800 KGM |