

xs7c40fp260

inductive sensor XS7 40x40x117 - plastic - Sn15mm - 24..240VAC - terminals



Main

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XS7
Sensor design	Form 40 x 40 x 117
Size	117 mm
Body type	Fixed
Detector flush mounting acceptance	Flush mountable
Material	Plastic
Enclosure material	Plastic
Type of output signal	Discrete
Wiring technique	2-wire
[Sn] nominal sensing distance	15 mm
Discrete output function	1 NO or 1 NC programmable
Output circuit type	AC
Electrical connection	Screw-clamp terminals, clamping capacity: 2 x 1.5 mm ²
[Us] rated supply voltage	24...240 V AC 50/60 Hz
Switching capacity in mA	5...500 mA
IP degree of protection	IP67 conforming to IEC 60529

Complementary

Detection face	5 positions turret head
Front material	Plastic
Operating zone	0...12 mm
Differential travel	3...20% of Sr
Repeat accuracy	<= 3% of Sr
Cable entry number	1 tapped entry for Pg 13.5 cable gland
Status LED	1 LED yellow for output state
Supply voltage limits	20...264 V AC
Residual current	<= 1.5 mA for open state
Switching frequency	<= 25 Hz
Voltage drop	<= 5.5 V at closed state
Delay first up	<= 120 ms
Delay response	<= 30 ms
Delay recovery	<= 20 ms
Marking	CE
Height	40 mm
Length	40 mm
Width	117 mm
Product weight	0.22 kg

Environment

Product certifications

CCC
CSA
C-Tick
UL

Ambient air temperature for operation

-25...70 °C

Offer Sustainability

Sustainable offer status

Green Premium product

RoHS

Compliant - since 0836 - Schneider Electric declaration of conformity

Product environmental profile

Available

Product end of life instructions

Available

