

Technical data sheet

Article number:
924-00495

BLT1.5

Product Group	Twin Bootlace Ferrules
Product Family	Nylon Insulated Twin Bootlace Terminals
Material	Copper (CU), Polyamide 6.6 (PA66)
Colour	Black (BK)
Application Range	Low Voltage
Conductor Size (mm²)	1.5 mm ²
Diameter (D)	6.6 mm
Halogen-free	Yes
Length (L)	16 mm
Length (L2)	8 mm
Length (L3)	8 mm
Max Voltage	600 V
Operating Temperature	-30 °C to +105 °C
Package Content packed in	bag
RECh Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Ø (D2)	2.2 mm
Width (W)	3.6 mm

HF ✓

RoHS ✓