


[Phones Without Answering Machine](#)
[Telephones With Single Handset](#)

Telephone KX-TGD310E

General	Colour	B[Black & Silver]/G[Carbon Gray & Silver]
	Cordless Handset (Quantity)	1
	Frequency	1.9 GHz
	Frequency Range	1.88 GHz - 1.90 GHz
	Number of Channels	120 Channels
	System	DECT
	DECT Security Mode	Y
	GAP	Y
	Number of Phone Lines	1
	Multiple Cordless Handsets Capability	Up to 6 Handsets
	Multiple Base Units Capability	Up to 4 Base Units
	LCD Language	Catalan, Danish, Dutch, English, Finnish, French, German, Greek, Italian, Norwegian, Portuguese Spanish, Swedish, Turkish
	Wi-Fi® Connection	-
	Mobile Connection	-
	Bluetooth® Class	-
	Android™ OS Version	-
Power Saving	Low Radio Power	Y
	One Touch Eco Mode	Y
Smartphone Connect		-
Multiple Smartphones Capability		-
Supported Devices		-

Wireless Network Standard		-
Simplified Configuration		-
Easy Wi-Fi Setup Button		-
Wi-Fi Repeater Mode		-
Phonebook Copy from Smartphone		-
Ringtone Copy from Smartphone		-
Wallpaper Image Copy from Smartphone		-
Conference Call with Outside Landline and Smartphone		-
Transferring Landline Call (between Smartphone and Handsets)		-
Playing Answering System Messages		-
Convenience	Key Finder Compatible	Y
	Multiple Key Finder Capability	Up to 4 Key Finders
	Repeater Available	Y
	Clear Sound	Y
	Noise Reduction (Cordless Handset)	-
	Noise Reduction (Answering System)	-
	Customized Sound System (Equalizer)	Treble/Alto/Bass
	Compatible with Hearing Aid T-Coil (TIA-1083 Compliant)	-
	Power Back-Up Operation	-
	Baby Monitor	Y/* Optional handset is required for the internal baby monitor feature.
	Smart Function Key	-
	Any Key Answer	Y

	Do Not Disturb Mode	Y
	Bypassing Do Not Disturb Mode (Specified Phonebook Category)	Y/* Requires subscription to Caller ID service offered by your provider/telephone company.
	SMS	-
	Call Restriction	Y
	Distress Call	-
	Conference Call with Outside Line	Y/3Way/* 3Way: Handset - Handset - Landline/** Optional handset is required.
	Call Share	Y/* Optional handset is required.
	Intercom (Cordless Handset to Base Unit)	-
	Intercom (Cordless Handset to Cordless Handset)	Y/* Optional handset is required.
	Intercom All	Y (To All Handsets)/* Optional handset is required.
	Clock	Y
	Calendar/Scheduler	-
	Alarm (Wake-up / Memo alarm)	Y/Y
	Advanced Alarm (A day of the week / Snooze)	Y/Y
	Bluetooth Headset Capability (HSP Support)	-
	Bluetooth Audio Headphone/Speaker Capability (A2DP Support)	-
	Google PlayTM Support	-
Caller ID/ Phonebook	Caller ID	Y/* Requires subscription to Caller ID service offered by your provider/telephone company.
	Caller ID Memory	50 items/* Requires subscription to Caller ID service offered by your provider/telephone company.
	Call Waiting Caller ID	Y/* Requires subscription to both Caller ID and Call Waiting with Caller ID services offered by your provider/telephone company.

	Category Display Colours	-
	Talking Caller ID (Cordless Handset)	-
	Talking Caller ID (Base Unit)	-
	Talking Caller ID Language	-
	Nuisance Call Block	Y(50 numbers)/* Requires subscription to Caller ID service offered by your provider/telephone company./** Requires number registration in the nuisance call block list.
	Block Range of Numbers	Y/* Requires subscription to Caller ID service offered by your provider/telephone company.
	Block Numberless Call	Y/* Requires subscription to Caller ID service offered by your provider/telephone company./** Numberless calls cannot be blocked depending on the service of your provider/telephone company.
	Handset Phonebook Memory (Name/Number)	-
	Base Unit Phonebook Memory (Name/Number)	120items/(16char/24digits)
	Shared Phonebook	Y/* Optional handset is required.
	Phonebook Copy from Mobile Phone via Bluetooth	-
	Chain Dial (Cordless Handset)	Y
	Chain Dial (Base Unit)	-
Cordless Handset	LCD	1.8 inch (4.6 cm)/Full Dot Monochrome/103 x 65 pixels
	LCD Backlight Colour	White
	Touchscreen	-
	Front Camera	-
	Rear Camera	-
	LED Flash	-
	GPS	-
	SD Memory Card Slot	-

	USB Jack	-
	USB Version	-
	Illuminated Keypad	Amber
	Speakerphone (Volume Steps)	Y(6-step)
	Full Duplex Speakerphone	-
	Icon Operation (Number of Icons)	Y(6)
	Ringer Pattern (Tone+Melody)	40
	Polyphonic Ringer Melody	32 chord
	Ringer Volume Steps	6+OFF
	Receiver Volume Steps	4
	Redial Memory	10(Name & Number)/* Requires registration in the phonebook to display the name.
	Digits of Redial Number	24
	Auto Redial	-
	Ringer Indicator (Colour)	-
	Hold	Y
	Mute	Y
	Key Lock	Y
	Headset Jack	-
	Secure Grip	-
	Short Stroke Key	Y
	Wall Mountable (Charger)	-
Base Unit	Dial Keypad	-
	Corded Handset	-
	Display	-

	Speakerphone (Volume Steps)	-
	Ringer Pattern (Tone+Melody)	-
	Ringer Volume Steps	-
	Redial Memory	-
	Auto Redial	-
	Mobile Locator	-
	Hold	-
	Mute	-
	Handset Locator	Y
	Wall Mountable	-
Answering System		-
Total Recording Time		-
Fast-Forwarding and Rewinding Message		-
Audible Message Alert		-
New Message Notification by a Call		-
Announcement Language of New Message Notification		-
New Message Notification by an SMS		-
Visual Message List (Handset LCD)		-
Recording Conversation		-
Speaker Volume Steps(Base Unit Speaker)		-
Call Screening (Cordless Handset)		-
Call Screening (Base Unit)		-
Language of Pre-recorded Greeting Message		-
Remote Operation from Outside (DTMF)		-
Toll Saver (New Messages Recorded / No		-

New Message)		
Accessories	Key Finder Included (Quantity)	-
	Repeater Included	-
	Belt Clip Included	-
Optional Handset		KX-TGDA30
Others	Radiation Free (Eco Mode Plus)	Y
	Rechargeable Battery	Ni-MH(AAA x 2)
	Talk Time	Up to 16hours
	Standby Time	Up to 200hours
	Charge Time	About 7 hours
Power Consumption	Base Unit Standby Power Consumption	0.52W
	Charger Standby Power Consumption	0.16W
Dimensions/ Weight	Base Unit Dimensions (W x D x H)	Approx. 90 mm× 109 mm× 85mm
	Charger Dimensions (W x D x H)	Approx. 69 mm× 69 mm× 36mm
	Key Finder Dimensions (W x D x H)	-
	Repeater Dimensions (W x D x H)	-
	Base Unit Weight	Approx. 120 g
	Charger Weight	Approx. 40 g
	Interface Box Weight	-
	Key Finder Weight	-
	Repeater Weight	-