

Datasheet

ENGLISH

# RS PRO Cable Gland Kits

Stock No: 1856093



Colour: Grey



## Business data

Product description	Sealing Element
Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	28
Weight per piece (including packaging)	28.4
Unit of weight	G
Customs number	39259020
Country of origin	DE

## Technical Specifications:

### Dimensions

Length	42.8 mm
Width	42.8 mm
Height	17.7 mm

### Materials

Material	TPE
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	90 °C
Halogen-free	✓
Silicone-free	✓

### Further technical data

Mounting type	Plug in
Protection	IP66
Strain relief	✓
Cable diameter, min.	19 mm
Cable diameter, max.	20 mm

### Further technical data

NEMA Type	4x
-----------	----

## Standards and regulations

Standards / specifications	Strain relief complying with DIN EN 62444
<b>cUL Recognized</b>	
cUL Recognized	C22.2 No. 14-95
cUL Recognized	✓
<b>UL Recognized</b>	
UL Recognized	UL 508
UL Recognized granted	✓