

A52.080/1, 0...120°C, 100x8mm

Bimetallic thermometer, for industrial applications A52L

Item number: 3903958

Quantity: 1 pcs.

Order code: A52.080-1-C1F-BS-C100GZZ-Z-ZZZ TD FZZVC-AZ1ZZZZZZZZZZ

Overview: A52.080/1, 0...120°C, 100x8mm
Process connection: plain, with neck to fit thermowell (thermowell necessary for mounting)
flat instrument glass
WIKA

Details: Bimetallic thermometer, for industrial applications A52L
Specifications according to data sheet: TM 52.01
Accuracy class: class 1 per EN 13190
Case: stainless steel
Stem material: stainless steel
Model: A52.080, nominal size 80, location of stem centre back
Connection design: 1, plain stem
Scale range: 0 °C ... 120 °C
Process connection: plain, with neck to fit thermowell (thermowell necessary for mounting)
Stem diameter: 8 mm
Insertion length L1: 100 mm
Window: flat instrument glass
Case: Stainless steel
Ingress protection: IP 43
Manufacturer logo: *WIKA*
Stem material: stainless steel