



Datasheet

ENGLISH

RS PRO Panel Mounting printer

Stock No: 178-5731



This RS Pro panel mount printer is compact fixed head thermal line printing mechanism. It has an electrical rating of 3.5VDC to 8.5VDC and 3A. RS232/Parallel Interface.

This printer has a resolution of 8dpmm with 384 dots per line.

Features and Benefits

Simple drop-in easy paper loading for operational efficiencies

Data input is USB 2.0 full-speed, RS-232 serial

Smart desktop size; Height of 110mm, width of 54mm, and 57mm of depth.

Paper width is 58.0mm

High performance thermal printer mechanisms ensure fast, reliable printing even at peak times

Reliable long-life expectancy of MCBF 5 million lines.

Robust, stylish design that is easily embedded into many devices.

Applications

Receipt printing

Medical/Healthcare equipment

POS Receipt printing

ATM Receipt printing

OEM Machines

Test and measurement